

EER-Ti/T Trapezoidal Deck Threaded Rod Hanger



FEATURES

Supports threaded rod

Thread impression for simple installation

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	E-Number	Hole Size (HS)	Hole Type	Flange Thickness (FT)	Drill Bit Diameter
EERTIM10	173140	1319466	10 mm	Threaded	0.8 - 3 mm	7mm
EERTIM6	173120	1319464	6 mm	Threaded	0.8 - 3 mm	7mm
EERTIM8	173130	1319465	8 mm	Threaded	0.8 - 3 mm	7mm

Table 2/2

Catalog Number	Article Number	E-Number	Static Load 1 (F1)	Static Load 2 (F2)	Certifications
EERTIM10	173140	1319466	450N	900N	ITB
EERTIM6	173120	1319464	450N	900N	
EERTIM8	173130	1319465	450N	900N	ITB

ADDITIONAL PRODUCT DETAILS

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

