

# Universal Restraint Clip, Slotted, #12, #18 Brace, M10 Rod

## CATALOG NUMBER

**CSBURCR38**

## FEATURES

Slotted design ideal for attaching to existing threaded rod on trapezes

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing



## PRODUCT ATTRIBUTES

Article Number: 402201

Material: Steel

Finish: Electrogalvanized

Brace Size: #12;#18

Rod Size (RS): 10


Thickness (T): 4.27 mm

## ADDITIONAL PRODUCT DETAILS

Brace member is not included.

| UL Loads    |              |             |
|-------------|--------------|-------------|
| Part Number | Brace Member | Load Rating |
| CSBURCR38   | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
| CSBURCR12   | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
| CSBURCR58   | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

