

EM-P Conduit to Flange Clip



FEATURES

Requires only a hammer to install

Available for EMT, rigid, IMT and aluminum conduit


Will pivot thru 360°

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)	Certifications
12P24	175110	1319495	22 - 30 mm	3 - 8 mm	110N	
12P58	175120	1319496	22 - 30 mm	8 - 14 mm	110N	
12P912	175130	1319497	22 - 30 mm	14 - 20 mm	110N	
16P24	175140	1319498	30 - 35 mm	3 - 8 mm	110N	
16P58	175150	1319499	30 - 35 mm	8 - 14 mm	110N	
16P912	175160	1319500	30 - 35 mm	14 - 20 mm	110N	
8P24	172150	1319451	18 - 22 mm	3 - 8 mm	110N	ITB
8P58	172160	1319452	18 - 22 mm	8 - 14 mm	110N	ITB
8P912	175100	1319494	18 - 22 mm	14 - 20 mm	110N	ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

