

Hammer-On Flange Clip, Bottom Mount



FEATURES

Can be used to support boxes, fixtures or other applications from beam flanges

Assorted attachment points provided to reduce inventory

Requires only a hammer to install



SPECIFICATIONS

Table 1/2



Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	Rod Size (RS)
EM1318	170075	1305721	Spring Steel	nVent CADDY Armour	21 - 28 mm	6
EM24	170050	1341042	Spring Steel	nVent CADDY Armour	3 - 8 mm	6
EM24S1	179720	1319531	Stainless Steel 301 (EN 1.4310)		3 - 8 mm	6
EM24SP25	172170	1340918	Spring Steel	nVent CADDY Armour	3 - 8 mm	6
EM58	170060	1341043	Spring Steel	nVent CADDY Armour	8 - 14 mm	6
EM58R5	191027	1319608	Spring Steel	nVent CADDY Armour	8 - 14 mm	6
EM58S1	179730	1341393	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	6

Catalog Number	Article Number	E- Number	Material	Finish	Flange Thickness (FT)	Rod Size (RS)
EM58SP25	172180	1340919	Spring Steel	nVent CADDY Armour	8 - 14 mm	6
EM912	170070	1341044	Spring Steel	nVent CADDY Armour	14 - 20 mm	6
EM912S1	179740	1319532	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	6
EM912SP25	175760	1340920	Spring Steel	nVent CADDY Armour	14 - 20 mm	6

Table 2/2

Catalog Number	Article Number	E- Number	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)	Certifications
EM1318	170075	1305721	450N	110N	330N	cUL, UL
EM24	170050	1341042	450N	110N	330N	ITB, CE, 4H, EM, EBC
EM24S1	179720	1319531	200N	110N	200N	
EM24SP25	172170	1340918	450N	110N	330N	CE, 4H, EM, EBC
EM58	170060	1341043	450N	110N	330N	ITB, CE, 4H, EM, EBC
EM58R5	191027	1319608	450N	110N	330N	CE, 4H, EM, EBC
EM58S1	179730	1341393	200N	110N	200N	
EM58SP25	172180	1340919	450N	110N	330N	CE, 4H, EM, EBC
EM912	170070	1341044	450N	110N	330N	ITB, CE, 4H, EM, EBC
EM912S1	179740	1319532	200N	110N	200N	
EM912SP25	175760	1340920	450N	110N	330N	CE, 4H, EM, EBC

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

