


Hammer-On Flange Clip, Side Mount

FEATURES

Provides an attachment for wire, S-hooks, chain, nVent CADDY Speed Link or other assemblies to flanges and profiles

Fits most beams

Installs with just a hammer



SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)
2H4	170010	1341011	Spring Steel	nVent CADDY Armour	2 - 3 mm	7.1 mm
4H1318	170045	1300219	Spring Steel	nVent CADDY Armour	21 - 28 mm	7.1 mm
4H24	170020	1341001	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm
4H24R5	191018	1319600	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm
4H24S1	179610	1319525	Stainless Steel 301 (EN 1.4310)		3 - 8 mm	7.1 mm
4H24SP25	172320	1340901	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm
4H58	170030	1341002	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm

Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)
4H58R5	191019	1319601	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm
4H58S1	179620	1319526	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	7.1 mm
4H58SP25	172350	1340902	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm
4H912	170040	1341003	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm
4H912R5	191045	1319618	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm
4H912S1	179630	1319527	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	7.1 mm
4H912SP25	172380	1340903	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm

Table 2/2

Catalog Number	Article Number	E-Number	Static Load	Certifications
2H4	170010	1341011	700N	ITB, UL, cUL
4H1318	170045	1300219	900N	cUL, UL
4H24	170020	1341001	900N	cUL, UL, CE, 4H, EM, EBC, ITB
4H24R5	191018	1319600	900N	CE, 4H, EM, EBC, cUL, UL
4H24S1	179610	1319525	650N	
4H24SP25	172320	1340901	900N	CE, 4H, EM, EBC
4H58	170030	1341002	900N	UL, CE, 4H, EM, EBC, cUL, ITB
4H58R5	191019	1319601	900N	cUL, CE, 4H, EM, EBC, UL
4H58S1	179620	1319526	650N	
4H58SP25	172350	1340902	900N	CE, 4H, EM, EBC
4H912	170040	1341003	900N	cUL, UL, CE, 4H, EM, EBC, ITB
4H912R5	191045	1319618	900N	CE, 4H, EM, EBC, cUL, UL
4H912S1	179630	1319527	650N	
4H912SP25	172380	1340903	900N	CE, 4H, EM, EBC



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

