

Heavy Duty Pipe Clamp

FEATURES

For high static requirements in industrial construction

Suitable for fix point applications



Material: Steel
Finish: Painted;Red Oxide

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	NB/DN	Hole Size (HS)	Screw Diameter (Sc)
SSG022RO	574600	3535149	20.5 - 22 mm	15	6.6 mm	6 mm
SSG028RO	574610	3535151	26.5 - 28 mm	20	6.6 mm	6 mm
SSG0359RO	574725		355 - 363 mm		22 mm	20 mm
SSG035RO	574620	3535152	33 - 35 mm	25	11 mm	10 mm
SSG043RO	574630	3535153	40 - 43 mm	32	11 mm	10 mm
SSG049RO	574640	3535154	48 - 49 mm	40	11 mm	10 mm
SSG061RO	574650	3535155	57.0 - 60.3 mm	50	11 mm	10 mm
SSG077RO	574660	3535156	75 - 77 mm	65	11 mm	10 mm
SSG090RO	574670	3535157	88 - 90 mm	80	11 mm	10 mm
SSG115RO	574680	3535158	110 - 115 mm	100	18 mm	16 mm
SSG141RO	574685	3535414	139 - 141 mm	125	18 mm	16 mm
SSG170RO	574690	3535159	165 - 170 mm	150	18 mm	16 mm


Catalog Number	Article Number	E-Number	Outer Diameter (OD)	NB/DN	Hole Size (HS)	Screw Diameter (Sc)
SSG222RO	574700	3535161	216 - 222 mm	200	22 mm	20 mm
SSG276RO	574710	3535882	267 - 276 mm	250	22 mm	20 mm
SSG327RO	574720	3535883	321 - 327 mm	300	22 mm	20 mm
SSG410RO	574730	3535884	403 - 410 mm	400	26 mm	24 mm

Table 2/2							
Catalog Number	Article Number	E-Number	Screw Length (L)	Static Load	Width (W)	Thickness (T)	A
SSG022RO	574600	3535149	20mm	1000N	23 mm	3 mm	46 mm
SSG028RO	574610	3535151	20mm	1000N	23 mm	3 mm	52 mm
SSG0359RO	574725		80mm	2600N	60 mm	8 mm	427 mm
SSG035RO	574620	3535152	40mm	1000N	40 mm	4 mm	71 mm
SSG043RO	574630	3535153	40mm	1000N	40 mm	4 mm	79 mm
SSG049RO	574640	3535154	40mm	1000N	40 mm	4 mm	85 mm
SSG061RO	574650	3535155	40mm	1800N	40 mm	4 mm	97 mm
SSG077RO	574660	3535156	40mm	1400N	40 mm	4 mm	113 mm
SSG090RO	574670	3535157	40mm	1200N	40 mm	4 mm	126 mm
SSG115RO	574680	3535158	60mm	2900N	50 mm	6 mm	167 mm
SSG141RO	574685	3535414	60mm	2500N	50 mm	6 mm	193 mm
SSG170RO	574690	3535159	60mm	2200N	50 mm	6 mm	222 mm
SSG222RO	574700	3535161	80mm	3600N	60 mm	8 mm	290 mm
SSG276RO	574710	3535882	80mm	3100N	60 mm	8 mm	344 mm
SSG327RO	574720	3535883	80mm	2800N	60 mm	8 mm	395 mm
SSG410RO	574730	3535884	80mm	4100N	70 mm	10 mm	492 mm

ADDITIONAL PRODUCT DETAILS

Static load refers to a complete set of Heavy Duty Pipe Clamps held in place with indicated screws per ISO 4014 and corresponding hex nuts per ISO 4032 (for further information, please refer to Standard SSG 7075E).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

