

Hex Head Bolt

FEATURES


Fully threaded hexagon head bolt

Material: Steel
Complies With: DIN 933

SPECIFICATIONS

Catalog Number	Article Number	E-Number	Finish	Screw Diameter (Sc)	Screw Length (L)
HSCRM1025HD	593745	1342867	Hot-Dip Galvanized	10	25mm
HSCRM1030HD	593755	1342868	Hot-Dip Galvanized	10	30mm
HSCRM825EG	593680		Electrogalvanized	8	25mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDDT](https://www.nvent.com/ENDDT)

