

KN Hook




FEATURES

Use to repair a link or combine two chains together by hammering the link shut

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Article Number	E-Number	Diameter (Ø)	Length (L)	B	Static Load
KN30EG	380050	1319828	3 mm	16.5mm	12.5 mm	370N
KN40EG	380060	1341094	4 mm	20mm	16 mm	550N
KN50EG	380070	1319829	5 mm	23mm	20 mm	950N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

