

nVent CADDY Macrofix Non-Insulated M8/M10



FEATURES

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)
MFN019EG	586101	3536031	15 - 19 mm	10	M8, M10	20 mm
MFN023EG	586102	3536032	19 - 23 mm	15	M8, M10	20 mm
MFN029EG	586103	3536033	23 - 29 mm	20	M8, M10	20 mm
MFN035EG	586104	3536034	29 - 35 mm	25	M8, M10	20 mm
MFN041EG	586105	3536035	35 - 41 mm		M8, M10	20 mm
MFN048EG	586106	3536036	41 - 48 mm	32	M8, M10	20 mm
MFN054EG	586107	3536037	48 - 54 mm	40	M8, M10	20 mm
MFN062EG	586108	3536038	54 - 62 mm	50	M8, M10	20 mm
MFN072EG	586109	3536039	62 - 72 mm		M8, M10	20 mm
MFN083EG	586110	3536041	73 - 83 mm	65	M8, M10	23 mm
MFN093EG	586111	3536042	83 - 93 mm	80	M8, M10	23 mm

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)
MFN103EG	586112	3536043	93 - 103 mm	90	M8, M10	23 mm
MFN113EG	586113	3536044	103 - 113 mm		M8, M10	23 mm
MFN123EG	586114	3536045	113 - 123 mm	100	M8, M10	23 mm
MFN133EG	586115	3536046	123 - 133 mm		M8, M10	23 mm
MFN143EG	586116	3536047	133 - 143 mm	125	M8, M10	23 mm
MFN153EG	586117	3533381	143 - 153 mm		M8, M10	25 mm
MFN165EG	586118	3533382	155 - 165 mm		M8, M10	25 mm
MFN175EG	586119	3533383	165 - 175 mm	150	M8, M10	25 mm
MFN205EG	586120	3533384	195 - 205 mm		M8, M10	27 mm

Table 2/2

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	NB/DN	Rod Size (RS)	Width (W)
MFN220EG	586121	3533385	210 - 220 mm	200	M8, M10	27 mm
MFN230EG	586122	3533386	220 - 230 mm		M8, M10	27 mm
MFN255EG	586123	3533387	244 - 255 mm		M8, M10	30 mm
MFN280EG	586124	3533388	270 - 280 mm	250	M8, M10	30 mm
MFN324EG	586125	3533389	314 - 324 mm	300	M8, M10	30 mm
MFN184EG	586126		175 - 184 mm		M8, M10	25 mm
MFN194EG	586127		185 - 194 mm		M8, M10	25 mm


Table 1/2

Catalog Number	Article Number	E-Number	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load	Certifications
MFN019EG	586101	3536031	1 mm	6	17mm	1000N	ITB DoC 2018 0396, RAL-GZ 655
MFN023EG	586102	3536032	1 mm	6	17mm	1000N	ITB DoC 2018 0396, RAL-GZ 655
MFN029EG	586103	3536033	1 mm	6	17mm	1000N	ITB DoC 2018 0396, RAL-GZ 655
MFN035EG	586104	3536034	1 mm	6	17mm	1000N	ITB DoC 2018 0396, RAL-GZ 655
MFN041EG	586105	3536035	1 mm	6	22mm	1000N	RAL-GZ 655, ITB DoC 2018 0396
MFN048EG	586106	3536036	1 mm	6	22mm	1000N	ITB DoC 2018 0396, RAL-GZ 655
MFN054EG	586107	3536037	1.25 mm	6	22mm	1500N	RAL-GZ 655, ITB DoC 2018 0396
MFN062EG	586108	3536038	1.25 mm	6	22mm	1500N	RAL-GZ 655, ITB DoC 2018 0396

Catalog Number	Article Number	E- Number	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load	Certifications
MFN072EG	586109	3536039	1.25 mm	6	22mm	1500N	RAL-GZ 655, ITB DoC 2018 0396
MFN083EG	586110	3536041	1.5 mm	6	27mm	2000N	RAL-GZ 655, ITB DoC 2018 0396
MFN093EG	586111	3536042	1.5 mm	6	27mm	2000N	ITB DoC 2018 0396, RAL-GZ 655
MFN103EG	586112	3536043	1.75 mm	6	27mm	2500N	ITB DoC 2018 0396, RAL-GZ 655
MFN113EG	586113	3536044	1.75 mm	6	27mm	2500N	RAL-GZ 655, ITB DoC 2018 0396
MFN123EG	586114	3536045	1.75 mm	6	27mm	2500N	RAL-GZ 655, ITB DoC 2018 0396
MFN133EG	586115	3536046	2 mm	6	27mm	3000N	RAL-GZ 655, ITB DoC 2018 0396
MFN143EG	586116	3536047	2 mm	6	27mm	3000N	ITB DoC 2018 0396, RAL-GZ 655
MFN153EG	586117	3533381	2 mm	6	27mm	3200N	ITB DoC 2018 0396, RAL-GZ 655
MFN165EG	586118	3533382	2 mm	6	27mm	3200N	ITB DoC 2018 0396, RAL-GZ 655
MFN175EG	586119	3533383	2 mm	6	27mm	3200N	RAL-GZ 655, ITB DoC 2018 0396
MFN205EG	586120	3533384	2.25 mm	6	32mm	3600N	RAL-GZ 655, ITB DoC 2018 0396

Table 2/2

Catalog Number	Article Number	E- Number	Thickness (T)	Screw Diameter (Sc)	Screw Length (L)	Static Load	Certifications
MFN220EG	586121	3533385	2.25 mm	6	32mm	3600N	RAL-GZ 655, ITB DoC 2018 0396
MFN230EG	586122	3533386	2.25 mm	6	32mm	3600N	RAL-GZ 655, ITB DoC 2018 0396
MFN255EG	586123	3533387	2.5 mm	6	32mm	4000N	ITB DoC 2018 0396, RAL-GZ 655
MFN280EG	586124	3533388	2.5 mm	6	32mm	4000N	RAL-GZ 655, ITB DoC 2018 0396
MFN324EG	586125	3533389	2.5 mm	6	32mm	4000N	RAL-GZ 655, ITB DoC 2018 0396
MFN184EG	586126		2 mm	6	27mm	3200N	RAL-GZ 655
MFN194EG	586127		2 mm	6	27mm	3200N	RAL-GZ 655



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

