

nVent CADDY Pyramid Universal Support



FEATURES

Captive stainless steel nuts allow for custom attachment methods to the support base including easy attachment of stainless steel strut, threaded rod or other project-specific hardware

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Includes square holes for creating an H-Frame with a 12" (305 mm) cross support (PBU16 only)

Base is manufactured from UV-stabilized thermoplastic material

Material:	Polyethylene;Polypropylene;Stainless Steel 18-8 (EN 1.4305)
Temperature:	-45 to 65 °C
Static Load Safety Factor:	3:1

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	E-Number	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)
PBU10M	360496	1319818	254 mm	318 mm	102 mm	201 mm
PBU16M	360497	1319819	406 mm	480 mm	102 mm	201 mm

Catalog Number	Article Number	E-Number	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)
PBU6M	360495	1319817	140 mm	196 mm	102 mm	150 mm




Table 2/3

Catalog Number	Article Number	E-Number	Thread Size (TS)	Hole Quantity	A	B
PBU10M	360496	1319818	M10	2	218 mm	
PBU16M	360497	1319819	M10	2	165 mm	
PBU6M	360495	1319817	M10	3	114 mm	57 mm

Table 3/3

Catalog Number	Article Number	E-Number	Surface Area	Static Load
PBU10M	360496	1319818	59355mm ²	4450N
PBU16M	360497	1319819	91613mm ²	6670N
PBU6M	360495	1319817	26452mm ²	1330N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

