

# nVent CADDY Superklip



## FEATURES

Closes and locks automatically when the pipe, tube or cable is inserted

One-piece clamp for fast and convenient installation

Fasten with either wood screw, dual threaded screw with or without collar, nail with collar, threaded rod, mounting plate or shot-fire bracket

**Material:** Xenoy®  
**Temperature:** -25 to 90 °C

## SPECIFICATIONS

| Catalog Number | Article Number | E-Number | Outer Diameter (OD) | Copper Tube Size | B       | C       | Static Load |
|----------------|----------------|----------|---------------------|------------------|---------|---------|-------------|
| 389001         | 389001         | 3535685  | 11.8 - 14.3 mm      | 3/8"             | 17.2 mm | 29.9 mm | 160N        |
| 389002         | 389002         | 3535686  | 14.3 - 16.8 mm      | 1/2"             | 19.5 mm | 32 mm   | 175N        |
| 389003         | 389003         | 3535687  | 16.8 - 19.5 mm      | 5/8"             | 20 mm   | 35.4 mm | 190N        |
| 389004         | 389004         | 3535688  | 19.5 - 21.8 mm      |                  | 20 mm   | 39.4 mm | 200N        |
| 389005         | 389005         | 3535689  | 21.8 - 24.8 mm      | 3/4"             | 20 mm   | 42 mm   | 215N        |
| 389006         | 389006         | 3535691  | 24.8 - 27.8 mm      |                  | 20.2 mm | 45.1 mm | 240N        |
| 389007         | 389007         | 3535692  | 27.8 - 31.2 mm      | 1"               | 20.2 mm | 48.9 mm | 260N        |
| 389008         | 389008         | 3535693  | 31.2 - 35.5 mm      | 1 1/4"           | 21 mm   | 54.4 mm | 300N        |

| Catalog Number | ArticleNumber | E-<br>Number | Outer Diameter(OD) | Copper TubeSize | B       | C       | StaticLoad |
|----------------|---------------|--------------|--------------------|-----------------|---------|---------|------------|
| 389009         | 389009        | 3435785      | 35.5 - 39.5 mm     | 1 1/4"          | 21 mm   | 59.4 mm | 320N       |
| 389011         | 389011        | 3535694      | 39.5 - 43.5 mm     | 1 1/2"          | 21 mm   | 64.2 mm | 360N       |
| 389013         | 389013        | 3435787      | 50.5 - 55.5 mm     | 2"              | 23 mm   | 78.7 mm | 400N       |
| 389017         | 389017        | 3435791      | 7.8 - 9.5 mm       | 1/4"            | 17.1 mm | 26.4 mm | 135N       |
| 389018         | 389018        | 3435792      | 9.5 - 11.8 mm      | 1/4"            | 17.1 mm | 26.4 mm | 150N       |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

