

PBF Two Hole Base Plate for Threaded Rod

FEATURES

Light duty with two holes and one nut/adaptor



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	E-Number	Material	Finish	Rod Size (RS)	Length (L)
PBRM10L120	587160		Steel	Electrogalvanized	10	120mm
PBRM10L80	587135		Steel	Electrogalvanized	10	80mm
PBRM12L120	587165	3535233	Steel	Electrogalvanized	12	120mm
PBRM8M10L120	587140	3533918	Steel	Electrogalvanized	8, 10	120mm
PBRM8M10L70S6	587175	3532001	Stainless Steel 316 (EN 1.4401)		8, 10	70mm
PBRM8M10L80	587145	3535232	Steel	Electrogalvanized	8, 10	80mm

Table 2/2

Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	A	B	C
PBRM10L120	587160		40 mm	4 mm	81 mm	18 mm	11 mm

Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	A	B	C
PBRM10L80	587135		30 mm	3 mm	50 mm	18 mm	9 mm
PBRM12L120	587165	3535233	40 mm	4 mm	81 mm	18 mm	11 mm
PBRM8M10L120	587140	3533918	40 mm	4 mm	81 mm	18 mm	11 mm
PBRM8M10L70S6	587175	3532001	33 mm	2 mm	48 mm	10 mm	8 mm
PBRM8M10L80	587145	3535232	30 mm	3 mm	50 mm	18 mm	9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

