

Quick Strut Nut



FEATURES

Provides fast universal attachment of threaded rod and hardware to standard strut profiles

Pre-assembled slide nut ready to use out of the box

Spring retains assembly in place until hardware is tightened

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Rod Size (RS)	A	B	C
QSNM10EG	592920	3532746	10	8 mm	4 mm	41 mm
QSNM12EG	592930	3532747	12	8 mm	4 mm	41 mm
QSNM6EG	592900	3532744	6	6 mm	4 mm	41 mm
QSNM8EG	592910	3532745	8	6 mm	4 mm	41 mm


Table 2/2

Catalog Number	Article Number	E-Number	Torque (TQ)	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
QSNM10EG	592920	3532746	55 N·m	4400N	4400N	4900N
QSNM12EG	592930	3532747		4400N	4700N	4900N
QSNM6EG	592900	3532744		2000N	2000N	2000N
QSNM8EG	592910	3532745	28 N·m	3300N	3300N	3300N

ADDITIONAL PRODUCT DETAILS

Static Load 1 represents 1.5 mm strut channel thickness. Static Load 2 represents 2.0 mm strut channel thickness. Static Load 3 represents 2.5 mm strut channel thickness.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

