

SC Cable Snap Clip



FEATURES

Easily supports cable and plastic conduit from flanges

Requires only a hammer to install

Material: Spring Steel
Finish: nVent CADDY Armour

SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	E-Number	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
24SC1011	187550	1341022	2 - 4 mm	10 - 11 mm	0.6 mm
24SC1214	187570	1341023	2 - 4 mm	12 - 14 mm	0.6 mm
24SC1518	187590	1341024	2 - 4 mm	15 - 18 mm	0.6 mm
24SC1518R25	191003	1319585	2 - 4 mm	15 - 18 mm	0.6 mm
24SC1924	187610	1341025	2 - 4 mm	19 - 24 mm	0.6 mm
24SC1924R25	191004	1319586	2 - 4 mm	19 - 24 mm	0.6 mm
24SC2530	187630	1341026	2 - 4 mm	25 - 30 mm	0.6 mm
24SC2530R25	191005	1319587	2 - 4 mm	25 - 30 mm	0.6 mm
24SC67	187510	1341020	2 - 4 mm	6 - 7 mm	0.6 mm
24SC78	187710	1319571	2 - 4 mm	7 - 8 mm	0.6 mm
24SC89	187530	1341021	2 - 4 mm	8 - 9 mm	0.6 mm
24SC910	187750	1319572	2 - 4 mm	9 - 10 mm	0.6 mm

Catalog Number	Article Number	E-Number	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
47SC1011	187540	1341029	4 - 7 mm	10 - 11 mm	0.6 mm
47SC1214	187560	1341030	4 - 7 mm	12 - 14 mm	0.6 mm
47SC1518	187580	1341031	4 - 7 mm	15 - 18 mm	0.6 mm
47SC1518R25	191009	1319591	4 - 7 mm	15 - 18 mm	0.6 mm
47SC1924	187600	1341032	4 - 7 mm	19 - 24 mm	0.6 mm
47SC1924R25	191010	1319592	4 - 7 mm	19 - 24 mm	0.6 mm
47SC2530	187620	1341033	4 - 7 mm	25 - 30 mm	0.6 mm
47SC2530R25	191011	1319593	4 - 7 mm	25 - 30 mm	0.6 mm

Table 2/2

Catalog Number	Article Number	E-Number	Flange Thickness (FT)	Outer Diameter (OD)	Thickness (T)
47SC67	187500	1341027	4 - 7 mm	6 - 7 mm	0.6 mm
47SC78	187720		4 - 7 mm	7 - 8 mm	0.6 mm
47SC89	187520	1341028	4 - 7 mm	8 - 9 mm	0.6 mm
47SC910	187760		4 - 7 mm	9 - 10 mm	0.6 mm
812SC1011	187660	1341036	8 - 12 mm	10 - 11 mm	0.6 mm
812SC1214	187670	1341037	8 - 12 mm	12 - 14 mm	0.6 mm
812SC1518	187680	1341038	8 - 12 mm	15 - 18 mm	0.6 mm
812SC1518R25	191015	1319597	8 - 12 mm	15 - 18 mm	0.6 mm
812SC1924	187690	1341039	8 - 12 mm	19 - 24 mm	0.6 mm
812SC1924R25	191016	1319598	8 - 12 mm	19 - 24 mm	0.6 mm
812SC2530	187700	1341040	8 - 12 mm	25 - 30 mm	0.6 mm
812SC2530R25	191017	1319599	8 - 12 mm	25 - 30 mm	0.6 mm
812SC67	187640	1341034	8 - 12 mm	6 - 7 mm	0.6 mm
812SC78	187730		8 - 12 mm	7 - 8 mm	0.6 mm
812SC89	187650	1341035	8 - 12 mm	8 - 9 mm	0.6 mm
812SC910	187770	1319573	8 - 12 mm	9 - 10 mm	0.6 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

