

SOSR Stand Off Two Hole Strap for CPVC Pipe



FEATURES

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Positions pipe 1-1/2" (38 mm) off the mounting surface eliminating the need for wooden spacer blocks

Can be mounted in both vertical and horizontal positions on concrete, steel and wood

Meets the UL® 203 stringent upward thrust requirement

UL® Listed as both a hanger and pipe restraint

Complies with static load requirements of NFPA® 13

Includes mounting screws

Can be used with 3TW backing nut on composite wood joist installations

Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	NB/DN	Hole Size (HS)	A	B
SOSR075	597805	3435984	20	5.1 mm	68 mm	92 mm
SOSR100	597806	3532807	25	5.1 mm	75 mm	94 mm
SOSR125	597807	3532808	32	5.1 mm	84 mm	92 mm
SOSR150	597808	3532809	40	5.1 mm	98 mm	114 mm
SOSR200	597809	3532811	50	5.1 mm	102 mm	133 mm

Table 2/2

Catalog Number	Article Number	E-Number	C	Thickness (T)	Hanger Spacing
SOSR075	597805	3435984	25.4 mm	1.3 mm	1.65 m Max
SOSR100	597806	3532807	25.4 mm	1.3 mm	1.8 m Max
SOSR125	597807	3532808	25.4 mm	1.61 mm	1.95 m Max
SOSR150	597808	3532809	25.4 mm	1.61 mm	2.1 m Max

Catalog Number	Article Number	E-Number	C	Thickness (T)	Hanger Spacing
SOSR200	597809	3532811	25.4 mm	1.61 mm	2.4 m Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical
 Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

