

TBHKM Trapezoidal Deck Hanger with Fixed Nut



FEATURES

Requires separate cross bolt and nut

Use TDHP perforation tool to punch hole in decking

Material: Steel
Finish: Electrogalvanized




SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Rod Size (RS)	A	B	C
TBHKM10	597583	3532711	10	97 mm	91.5 mm	25 mm
TBHKM8	597582	1341306	8	97 mm	91.5 mm	25 mm

Table 2/2

Catalog Number	Article Number	E-Number	Thickness (T)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Certifications
TBHKM10	597583	3532711	2.5 mm	10.5 mm	5 mm	FM Approved, Pipe Hanger Components, VdS G4060082, ITB
TBHKM8	597582	1341306	2.5 mm	10.5 mm	5 mm	VdS G4060082, ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

