

TDHM Trapezoidal Deck Hanger with Threaded Nut



FEATURES

Easy install


Use TDHP perforation tool to punch hole in decking

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Article Number	E-Number	Rod Size (RS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Hole Size 3 (HS3)	D
TDHM10	179950	1341305	10	6.8 mm	14 mm	10 1/2mm	50 mm Max
TDHM6	179930	1319536	6	6.8 mm	14 mm	10 1/2mm	50 mm Max
TDHM8	179940	1341303	8	6.8 mm	14 mm	10 1/2mm	50 mm Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

