

Plain Doors, DN



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Table 1/3

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN1106R5		1082mm	593mm	17mm	Plain	Free-Standing

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN1206LR5	2411164	1182mm	593mm	17mm	Left Door	Free-Standing
DN1206R5	2411165	1182mm	593mm	17mm	Plain	Free-Standing
DN1206RR5	2411166	1182mm	593mm	17mm	Right Door	Free-Standing
DN1208R5	2411167	1182mm	793mm	17mm	Plain	Free-Standing
DN1405LR5	2411168	1382mm	493mm	17mm	Left Door	Free-Standing
DN1405RR5	2411169	1382mm	493mm	17mm	Right Door	Free-Standing
DN1406LR5	2411170	1382mm	593mm	17mm	Left Door	Free-Standing
DN1406R5	2411171	1382mm	593mm	17mm	Plain	Free-Standing
DN1406RR5	2411172	1382mm	793mm	17mm	Right Door	Free-Standing
DN1408R5		1382mm	793mm	17mm	Plain	Free-Standing
DN1606LR5		1582mm	593mm	17mm	Left Door	Free-Standing
DN1606R5		1582mm	593mm	17mm	Plain	Free-Standing
DN1606RR5		1582mm	593mm	17mm	Right Door	Free-Standing
DN1608R5		1582mm	793mm	17mm	Plain	Free-Standing
DN1610R5		1582mm	993mm	17mm	Plain	Free-Standing
DN1804LR5	2411175	1782mm	393mm	17mm	Left Door	Free-Standing
DN1804RR5	2411177	1782mm	393mm	17mm	Right Door	Free-Standing
DN1805LR5	2411178	1782mm	493mm	17mm	Left Door	Free-Standing
DN1805R5	2411179	1782mm	493mm	17mm	Plain	Free-Standing

Table 2/3

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN1805RR5	2411180	1782mm	493mm	17mm	Right Door	Free-Standing
DN1806LR5	2411181	1782mm	593mm	17mm	Left Door	Free-Standing
DN1806R5	2411182	1782mm	593mm	17mm	Plain	Free-Standing
DN1806RR5	2411183	1782mm	593mm	17mm	Right Door	Free-Standing
DN1808LR5	2411184	1782mm	793mm	17mm	Left Door	Free-Standing
DN1808R5	2411185	1782mm	793mm	17mm	Plain	Free-Standing
DN1808RR5	2411186	1782mm	793mm	17mm	Right Door	Free-Standing
DN1810R5	2411187	1782mm	993mm	17mm	Plain	Free-Standing
DN2004LR5	2411188	1982mm	393mm	17mm	Left Door	Free-Standing
DN2004RR5	2411190	1982mm	393mm	17mm	Right Door	Free-Standing
DN2005LR5	2411191	1982mm	493mm	17mm	Left Door	Free-Standing
DN2005R5	2411192	1982mm	493mm	17mm	Plain	Free-Standing
DN2005RR5	2411193	1982mm	493mm	17mm	Right Door	Free-Standing
DN2006LR5	2411194	1982mm	593mm	17mm	Left Door	Free-Standing
DN2006R5	2411195	1982mm	593mm	17mm	Plain	Free-Standing

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN2006RR5	2411196	1982mm	593mm	17mm	Right Door	Free-Standing
DN2008LR5	2411197	1982mm	793mm	17mm	Left Door	Free-Standing
DN2008R5	2411198	1982mm	793mm	17mm	Plain	Free-Standing
DN2008RR5	2411199	1982mm	793mm	17mm	Right Door	Free-Standing
DN2010R5	2411200	1982mm	993mm	17mm	Plain	Free-Standing

Table 3/3

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN2205LR5	2411202	2182mm	493mm	17mm	Left Door	Free-Standing
DN2205RR5	2411203	2182mm	493mm	17mm	Right Door	Free-Standing
DN2206LR5	2411204	2182mm	593mm	17mm	Left Door	Free-Standing
DN2206R5	2411205	2182mm	593mm	17mm	Plain	Free-Standing
DN2206RR5	2411206	2182mm	593mm	17mm	Right Door	Free-Standing
DN2208R5	2411207	2182mm	793mm	17mm	Plain	Free-Standing
DN1804R5		1782mm	393mm	17mm	Plain	Free-Standing
DN2004R5		1982mm	393mm	17mm	Plain	Free-Standing
DN2204R5		2182mm	393mm	17mm	Plain	Free-Standing
DN2210R5		2182mm	993mm	17mm	Plain	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.