

Plastic Cable Glands For Wall Mounted Enclosures, CPG



The compression of each cable fitted in this cable gland can be adjusted, and is secured using a locking nut, which provides strain relief as well as a high ingress protection.

FEATURES

Description: Traditional cable fittings. Known for excellent strain relief even while providing a high protection class. Plastic lock nuts for fixation are included in the delivery.

Material: Fitting body made of polyamide PA6, and sealing made of neoprene.

Temperature resistance: -20°C to +100°C.

Flammability: V-2 according to UL94.

Finish: RAL 7035.

Protection: IP 66

Material: Polyamide 6; Neoprene
Finish: Smooth
Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
CPG12	2411111	31mm	15mm	17mm	Mild Steel	Wall Mounted
CPG16	2411112	40mm	22mm	24mm	Mild Steel	Wall Mounted

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
CPG20	2411113	40mm	24mm	26mm	Mild Steel	Wall Mounted
CPG25	2411114	46mm	33mm	35mm	Mild Steel	Wall Mounted
CPG32	2411115	56mm	42mm	44mm	Mild Steel	Wall Mounted
CPG40	2411116	68mm	53mm	55mm	Mild Steel	Wall Mounted
CPG50	2411117	71mm	60mm	62mm	Mild Steel	Wall Mounted
CPG63	2411118	71mm	65mm	67mm	Mild Steel	Wall Mounted

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

