


Split Bottom Plates Stainless Steel, CBPS



A split bottom plate offers a flexible cabling solution and eliminates the need for individual cable glands. The protection degree is maintained by using a separate gasket.

FEATURES

Description: Fitted in place of the standard one piece bottom plate, allows direct cable entry. To achieve perfect sealing around the cables use the gasket kit BG01.

Material: AISI 304 / AISI 316L pre-grained stainless steel.

Bottom plates: 1.5 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 kit of two part bottom plate.

Finish: Brushed

Thickness: 1.5mm

SPECIFICATIONS

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Material
CBPS0640	2411031	25mm	600mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0640-316	2411032	25mm	600mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0650	2411033	25mm	600mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0650-316	2411034	25mm	600mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0660	2411035	25mm	600mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0660-316	2411036	25mm	600mm	600mm	Stainless Steel	Stainless Steel 316
CBPS0840	2411037	25mm	800mm	400mm	Stainless Steel	Stainless Steel 304
CBPS0840-316	2411038	25mm	800mm	400mm	Stainless Steel	Stainless Steel 316
CBPS0850	2411039	25mm	800mm	500mm	Stainless Steel	Stainless Steel 304
CBPS0850-316	2411040	25mm	800mm	500mm	Stainless Steel	Stainless Steel 316
CBPS0860	2411041	25mm	800mm	600mm	Stainless Steel	Stainless Steel 304
CBPS0860-316	2411042	25mm	800mm	600mm	Stainless Steel	Stainless Steel 316
CBPS1040	2411043	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 304
CBPS1040-316	2411044	25mm	1000mm	400mm	Stainless Steel	Stainless Steel 316

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Material
CBPS1050	2411045	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 304
CBPS1050-316	2411046	25mm	1000mm	500mm	Stainless Steel	Stainless Steel 316
CBPS1060	2411047	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 304
CBPS1060-316	2411048	25mm	1000mm	600mm	Stainless Steel	Stainless Steel 316

ADDITIONAL PRODUCT DETAILS

For enclosures 1200 mm & 1600 mm wide use 2 x 600 mm & 2 x 800 mm wide bottom plates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

