

Angle Bracket




FEATURES

Provides an attachment for nVent CADDY Speed Link assemblies, wire, threaded rod, S-hooks, or chain from concrete or wood

Finish: Hot-Dip Galvanized

SPECIFICATIONS

Catalog Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Height (H)	Length (L)	Width (W)	Thickness (T)	Static Load
AB1111	11 mm	11 mm	37 mm	37mm	25 mm	3 mm	700N
AB711	11 mm	7 mm	37 mm	37mm	25 mm	3 mm	700N
AB77	7 mm	7 mm	37 mm	37mm	25 mm	3 mm	700N
AB97	9 mm	7 mm	37 mm	37mm	25 mm	3 mm	700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

