

nVent CADDY Rod Lock L-Bracket, M10 Rod

CATALOG NUMBER

CRLLM10EG



FEATURES

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Multiple attachment holes support the use of either self-drilling screws or bolts, offering installation options for concrete, wood, and steel structures

Lock nut can be finger tightened, locking the rod in place

Integrated adjustment nut enables fine tuning the system height up or down

Extremely useful in tight spaces where wrenches are difficult to use

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 19 and 23)



PRODUCT ATTRIBUTES

Article Number: 390012

Material: Steel

Finish: Electrogalvanized

Rod Size (RS): 10

Height (H): 61.3 mm

Length (L): 43.2mm

Width (W): 35.6 mm

Hole Size 1 (HS1): 10.4 mm

Hole Size 2 (HS2): 7.1 mm

Wrench Size: 24 mm


Static Load: 3100N

ADDITIONAL PRODUCT DETAILS

Follow fastener manufacturer's recommended shear and pull-out strength when fastening to the structure. Fastener not included.

Install in accordance with applicable code.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/CADDY

