

nVent CADDY EPB Plus Loop Hanger, Flared Edges, 1 1/4" Pipe, 32 DN, 43 mm OD, M10 Rod



CATALOG NUMBER

EPB0125

FEATURES

For steel and CPVC pipe

Flared edges help to protect plastic pipe

Hexagon nuts not included



PRODUCT ATTRIBUTES

Article Number: 279503

Nut Included: No

Material: Steel

Finish: Electrogalvanized

Pipe Size: 1 1/4" Min

NB/DN: 32

Outer Diameter (OD): 43 mm

Rod Size (RS): M10

Height 1 (H1): 50mm

Height 2 (H2): 93mm

Width (W): 22 mm

Thickness (T): 1.2 mm

Static Load: 1330N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

