


Internal U-Shaped Coupler



Material: Steel

SPECIFICATIONS

Catalog Number	Article Number	Finish	Strut Type	Length (L)	Screw Included	Screw Diameter (Sc)	Screw Length (L)
ZU405PG	387805	Pregalvanized	A (41 x 41 mm)	250mm	Yes	6	12mm
ZUA404	387790	Hot-Dip Galvanized	C (21 x 41 mm)	250mm	No		
ZUA405	387800	Hot-Dip Galvanized	A (41 x 41 mm)	250mm	No		



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

