

# nVent CADDY Speed Link SLK with Shot-Fire Bracket



## FEATURES

Complete system includes wire, locking device and shot-fire bracket with pre-assembled drive pin from Powers Fasteners, Inc.

Quickly and easily attaches to concrete, steel or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

ICC-ES ESR-2024 evaluation report available for drive pin from DEWALT®

**Material:** Steel;Zinc Alloy;Polypropylene  
**Finish:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Complies With:** SMACNA HVAC-DCS



## SPECIFICATIONS

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | A       | B      | C       | Static Load |
|----------------|----------------|--------------------|------------------|---------|--------|---------|-------------|
| SLK15L1SF      | 196517         | 1.5 mm             | 1m               | 37.5 mm | 7.6 mm | 31.8 mm | 195N        |
| SLK15L2SF      | 196518         | 1.5 mm             | 2m               | 37.5 mm | 7.6 mm | 31.8 mm | 195N        |
| SLK15L3SF      | 196519         | 1.5 mm             | 3m               | 37.5 mm | 7.6 mm | 31.8 mm | 195N        |
| SLK15L5SF      | 196520         | 1.5 mm             | 5m               | 37.5 mm | 7.6 mm | 31.8 mm | 195N        |
| SLK2L2SF       | 196546         | 2 mm               | 2m               | 37.5 mm | 7.6 mm | 31.8 mm | 440N        |

**Height (H):** 55 mm  
**Width (W):** 19 mm  
**Thickness (T):** 12.5 mm  
**Angle (a):** 90 ° Max

ADDITIONAL PRODUCT DETAILS


Uses Powers Fasteners, Inc. part number 50032.

Static load was established based on a 1" (25.4 mm) embedment depth and 3,000 psi (20.68 MPa) lightweight concrete. For variations in embedment and material please consult [anchors.dewalt.com](http://anchors.dewalt.com).

Pre-assembled drive pin from Powers Fasteners, Inc. works with Powers® C4CZ, Simpson® GCN-MEPKT, SPIT® P1000, P200, P2201, P3500 / PA3500, P35s, P45, P60, P7201, Sniper; Ramset® 721, Cobra, D45 / D60 / D60L, M70, SA270, T3SS, TS750P, TS60P, Viper; Hilti® DX35, DX350 / DX351 / DX36M, DX100 / DX200, DX460, DXA40, DXA41, DXE72 / DX400; Würth® Diva-1, BST-1, BST-2 or equivalent nailers.

For shot-fired supports in seismic design category D, E, or F, maximum load is the lesser of 90 lb (400 N) or the published load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

