

nVent CADDY Cat HP J-Hook Tree, Ceiling Mount



FEATURES

Ideal for attaching to concrete, steel or wood surfaces

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Ready to use out of the box, saving installation time and labor

Requires no screws, rivets or special tools for assembly

Single- or double-sided tree configurations provide multiple J-Hooks with one structural attachment

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

Material: Steel
Finish: Pregalvanized

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Type	Diameter (Ø)	Tiers	Height (H)	Width (W)
CAT32HPDCM2	181049	Double Sided	50 mm	2	260 mm	148 mm
CAT32HPDCM3	181051	Double Sided	50 mm	3	387 mm	148 mm
CAT32HPDCM4	181052	Double Sided	50 mm	4	514 mm	148 mm

Catalog Number	Article Number	Type	Diameter (Ø)	Tiers	Height (H)	Width (W)
CAT32HPSCM2	181046	Single Sided	50 mm	2	260 mm	84.8 mm
CAT32HPSCM3	181047	Single Sided	50 mm	3	387 mm	84.8 mm
CAT32HPSCM4	181048	Single Sided	50 mm	4	514 mm	84.8 mm
CAT64HPDCM2	181057	Double Sided	100 mm	2	387 mm	254 mm
CAT64HPDCM3	181058	Double Sided	100 mm	3	578 mm	254 mm
CAT64HPDCM4	181059	Double Sided	100 mm	4	768 mm	254 mm
CAT64HPSCM2	181053	Single Sided	100 mm	2	387 mm	138 mm
CAT64HPSCM3	181054	Single Sided	100 mm	3	578 mm	138 mm
CAT64HPSCM4	181056	Single Sided	100 mm	4	768 mm	138 mm

Table 2/2

Catalog Number	Article Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	A	B	Static Load 1 (F1)	Static Load 2 (F2)
CAT32HPDCM2	181049	10.3 mm	4.7 mm	36.5 mm	50 mm	1080N	810N
CAT32HPDCM3	181051	10.3 mm	4.7 mm	36.5 mm	50 mm	1620N	810N
CAT32HPDCM4	181052	10.3 mm	4.7 mm	36.5 mm	50 mm	2160N	810N
CAT32HPSCM2	181046	10.3 mm	4.7 mm	36.5 mm	50 mm	540N	540N
CAT32HPSCM3	181047	10.3 mm	4.7 mm	36.5 mm	50 mm	810N	810N
CAT32HPSCM4	181048	10.3 mm	4.7 mm	36.5 mm	50 mm	1080N	810N
CAT64HPDCM2	181057	10.3 mm	4.7 mm	36.5 mm	50 mm	1080N	810N
CAT64HPDCM3	181058	10.3 mm	4.7 mm	36.5 mm	50 mm	1620N	810N
CAT64HPDCM4	181059	10.3 mm	4.7 mm	36.5 mm	50 mm	2160N	810N
CAT64HPSCM2	181053	10.3 mm	4.7 mm	36.5 mm	50 mm	540N	540N
CAT64HPSCM3	181054	10.3 mm	4.7 mm	36.5 mm	50 mm	810N	810N
CAT64HPSCM4	181056	10.3 mm	4.7 mm	36.5 mm	50 mm	1080N	810N


ADDITIONAL PRODUCT DETAILS

Static loads represent maximum load limit of J-Hook tree. Static load limit of each J-Hook is 60 lb (270 N).

Refer to Static Load 1 when fastening J-Hook tree using Hole Size 1. Refer to Static Load 2 when fastening J-Hook tree using Hole Size 2.

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

