

# Multi-Function C-Clamp, S304, 30–44 mm Flange



## CATALOG NUMBER

**C45S4**

## FEATURES

Multi-functional beam clamp

Use with Cable/Conduit/Pipe Clamp or Square Washer for Multi-Function C-Clamp

## PRODUCT ATTRIBUTES

Article Number: 336150

Material: Stainless Steel 304 (EN 1.4301)

Flange Thickness (FT): 30 - 44 mm

Hole Size (HS): 14 mm

Screw Diameter (Sc): 8

Screw Length (L): 30mm

Torque (TQ): 3 N·m

Static Load: 1100N

## ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

