


# nVent CADDY Cat HP J-Hook Clip to Pedestal Clamp



## FEATURES

Easy installation to pedestals used under raised floors

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability

Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook

**Material:** Steel;Spring Steel  
**Finish:** Electrogalvanized;nVent CADDY Armour



## SPECIFICATIONS

| Catalog Number | Article Number | Pedestal Size                      | Static Load |
|----------------|----------------|------------------------------------|-------------|
| CATHPCD0B      | 181085         | 19 mm Round                        | 70N         |
| CATHPCD1B      | 181086         | 19 mm Square, 22.2 - 28.5 mm Round | 70N         |
| CATHPCD2.5B    | 181088         | 25.4 mm Square                     | 70N         |
| CATHPCD2B      | 181087         | 22.2 mm Square                     | 70N         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDD1](https://www.nvent.com/ENDD1)

