

ROL15 Strut Mounted Roller, 18"–24" Pipe


CATALOG NUMBER

ROL15000EG

FEATURES

Designed for strut mounting

For applications where there is longitudinal pipe movement



PRODUCT ATTRIBUTES


Material: Steel

Finish: Electrogalvanized

Pipe Size: 18" - 24"

Pipe Size	Saddle Number	Covering Thickness	Outer Diameter	Radius	A	B
18"	None	0 mm	457.2 mm	228.6 mm	393.7 mm	301.6 mm
	631	38.1 mm	542.9 mm	271.5 mm	411.2 mm	341.3 mm
	632	50.8 mm	568.3 mm	284.2 mm	415.9 mm	354.0 mm
	633	63.5 mm	568.3 mm	296.9 mm	420.7 mm	366.7 mm
	634	76.2 mm	619.1 mm	309.6 mm	425.5 mm	379.4 mm
	635	101.6 mm	669.9 mm	335.0 mm	436.6 mm	404.8 mm
20"	None	0 mm	508.0 mm	254.0 mm	406.4 mm	309.6 mm
	631	38.1 mm	593.7 mm	296.9 mm	420.7 mm	366.7 mm
	632	50.8 mm	619.1 mm	309.6 mm	428.6 mm	377.8 mm
	633	63.5 mm	644.5 mm	322.3 mm	430.2 mm	392.1 mm
	634	76.2 mm	669.9 mm	335.0 mm	436.6 mm	403.2 mm
	635	101.6 mm	720.7 mm	360.4 mm	444.5 mm	430.2 mm
24"	None	0 mm	609.6 mm	304.8 mm	427.0 mm	376.2 mm
	631	38.1 mm	698.5 mm	349.2 mm	444.5 mm	415.9 mm
	632	50.8 mm	723.9 mm	362.0 mm	444.5 mm	428.6 mm
	633	63.5 mm	749.3 mm	374.6 mm	449.3 mm	441.3 mm
	634	76.2 mm	774.7 mm	387.3 mm	454.0 mm	454.0 mm
	635	101.6 mm	825.5 mm	412.7 mm	460.4 mm	479.4 mm
30"	Special Order	0 mm	762.0 mm	381.0 mm	452.4 mm	452.4 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

