



Combinations of horizontal rails and side panels

$u^{*}=v$ can be combined, $u^{*}=v^{*}$ combination not recommended

	side panel 1	side panel 2	side panel 3	side panel 4
horizontal rail 1				
horizontal rail 2				
horizontal rail 3				
horizontal rail 4				

Horizontal rail 1: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Horizontal rail 2: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Horizontal rail 3: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Horizontal rail 4: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Side panel 1: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Side panel 2: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Side panel 3: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

Side panel 4: 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm, 100 mm x 10 mm

34566-320

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



PRODUCT ATTRIBUTES

Rack Width: 20HP

Package Quantity: 1

Finish: Anodized

Length: 106.68mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, LD

Works With: Subracks

Net Weight: 0.03kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

