


# Cantilever Arm with E0 Channel

## FEATURES

Perforated, cold rolled

Slotted backplate



**Material:** Steel  
**Finish:** Electrogalvanized




## SPECIFICATIONS

| Catalog Number | Article Number | Length (L) |
|----------------|----------------|------------|
| CE015H0180EG   | 599885         | 180mm      |
| CE015H0240EG   | 599890         | 240mm      |
| CE015H0300EG   | 599900         | 300mm      |
| CE015H0360EG   | 599905         | 360mm      |
| CE015H0420EG   | 599910         | 420mm      |
| CE015H0540EG   | 599920         | 540mm      |
| CE015H0660EG   | 599925         | 660mm      |
| CE015H0780EG   | 599930         | 780mm      |

**Height (H):** 120 mm  
**Width (W):** 40 mm  
**Thickness (T):** 1.5 mm  
**A:** 30 mm  
**B:** 27 mm  
**C:** 15.5 mm

**D:** 60 mm  
**E:** 6 mm  
**X:** 11 x 18 mm  
**Y:** 8.5 x 20 mm  
**Hole Size (HS):** 10.5 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
 Option 1 – Customer Care  
 Option 2 – Technical  
 Support

Europe

Netherlands:  
 +31 800-0200135  
 France:  
 +33 800 901 793

Europe

Germany:  
 800 1890272  
 Other Countries:  
 +31 13 5835404

APAC

Shanghai:  
 + 86 21 2412 1618/19  
 Sydney:  
 +61 2 9751 8500

