

# Oval Pipe Clamp with Nut

## FEATURES

Designed to support pre-insulated twin tubes and integrated power cable for solar heat collectors

Shape of clamp provides a stable attachment to wall or ceiling



**Material:** Steel  
**Finish:** Electrogalvanized

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | NB/DN  | Rod Size (RS) | A     | B      | Width (W) |
|----------------|----------------|--------|---------------|-------|--------|-----------|
| MXOVDN1012EG   | 401161         | 10, 12 | M8, M10       | 30 mm | 69 mm  | 20 mm     |
| MXOVDN1215EG   | 401244         | 12, 15 | M8, M10       | 43 mm | 78 mm  | 20 mm     |
| MXOVDN1618EG   | 401245         | 16, 18 | M8, M10       | 51 mm | 88 mm  | 20 mm     |
| MXOVDN20EG     | 401246         | 20     | M8, M10       | 58 mm | 108 mm | 20 mm     |
| MXOVDN25EG     | 403800         | 25     | M8, M10       | 71 mm | 124 mm | 20 mm     |

Table 2/2

| Catalog Number | Article Number | Thickness (T) | Screw Diameter (Sc) | Screw Length (L) |
|----------------|----------------|---------------|---------------------|------------------|
| MXOVDN1012EG   | 401161         | 2 mm          | 6                   | 20mm             |
| MXOVDN1215EG   | 401244         | 2 mm          | 6                   | 20mm             |
| MXOVDN1618EG   | 401245         | 2 mm          | 6                   | 20mm             |
| MXOVDN20EG     | 401246         | 2 mm          | 6                   | 20mm             |
| MXOVDN25EG     | 403800         | 2 mm          | 6                   | 20mm             |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

