


# Speedway Cable Ladder Equal Tee



## FEATURES

- Creates a quick and easy equal tee pathway intersection
- Provides optimal support for high-performance low voltage and data cables
- Innovative SPEEDLOK integrated coupling system
- Safety edge protects cables during installation
- Slotted side channel, eliminating field drilling for cut-to-length applications
- IEC 61537 load rating and earthing compliant
- Responsive design and layout services, including seismic

**Material:** Steel  
**Finish:** Hot-Dip Galvanized



## SPECIFICATIONS

Table 1/2


| Catalog Number | Article Number | Width (W) | Angle (a) | A      | B      | C      |
|----------------|----------------|-----------|-----------|--------|--------|--------|
| CL110X150ETHD  | 840700         | 150 mm    | 90 °      | 900 mm | 450 mm | 950 mm |
| CL110X300ETHD  | 840710         | 300 mm    | 90 °      | 900 mm | 525 mm | 950 mm |
| CL110X450ETHD  | 840720         | 450 mm    | 90 °      | 900 mm | 600 mm | 950 mm |
| CL110X600ETHD  | 840730         | 600 mm    | 90 °      | 900 mm | 675 mm | 950 mm |
| CL110X750ETHD  | 840740         | 750 mm    | 90 °      | 900 mm | 750 mm | 950 mm |
| CL110X900ETHD  | 840750         | 900 mm    | 90 °      | 900 mm | 825 mm | 950 mm |

Table 2/2

| Catalog Number | Article Number | D     | E      |
|----------------|----------------|-------|--------|
| CL110X150ETHD  | 840700         | 80 mm | 110 mm |
| CL110X300ETHD  | 840710         | 80 mm | 110 mm |
| CL110X450ETHD  | 840720         | 80 mm | 110 mm |
| CL110X600ETHD  | 840730         | 80 mm | 110 mm |

| Catalog Number | Article Number | D     | E      |
|----------------|----------------|-------|--------|
| CL110X750ETHD  | 840740         | 80 mm | 110 mm |
| CL110X900ETHD  | 840750         | 80 mm | 110 mm |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

