

Cable Tie with Flange Clip, S301, 8–14 mm Flange, S302 Tie

CATALOG NUMBER

4H58CTBRS1

FEATURES

Used to support cables from beam flanges

Requires only a hammer to install

Comes complete with zip-tie



PRODUCT ATTRIBUTES

Article Number: 170300

Material: Stainless Steel 301 (EN 1.4310)

Flange Thickness (FT): 8 - 14 mm

Cable Tie: Stainless Steel 302 (EN 1.4324)

Diameter (Ø): 25 - 51 mm

Static Load: 300N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

