


MTVB Gravity Toggle with Rubber Washer

FEATURES

Complete with rod, nut, washer and load distribution block

Threaded rod is secured against unintentional removal

Approved for use in stationary fire protection systems (for pipes up to 2")



Material: Steel
Finish: Electrogalvanized




SPECIFICATIONS

Catalog Number	Article Number	Rod Size (RS)	Length (L)	Drill Bit Diameter	Static Load	Ultimate Static Load (F)	Certifications
MTVB10100	584465	10	100mm	25mm	800N	20kN	VdS G412037, FM Approved, Pipe Hanger Components
MTVB10200	584466	10	200mm	25mm	800N	20kN	FM Approved, Pipe Hanger Components
MTVB8100	584455	8	100mm	22mm	800N	20kN	VdS G412037
MTVB8200	584456	8	200mm	22mm	800N	20kN	VdS G412037

ADDITIONAL PRODUCT DETAILS

Static Load represents the maximum recommended load when fixed to a trapezoidal sheet.

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

