

APX External Vertical Wall Bracket



FEATURES

Saddle support for C-Profiles and strut

Complete with fixings

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	E-Number	Material	Finish	Channel Type	Strut Type
APXE01EG	584715	1522783	Steel	Electrogalvanized	E0L, E0, E1	
APXE23EG	584710	1522784	Steel	Electrogalvanized	E2L, E2, E3	
APXE4STRUTEG	584725	1522787	Steel	Electrogalvanized	E4	A (41 x 41 mm), C (21 x 41 mm)
APXSTRUTS6	584820		Stainless Steel 316 (EN 1.4401)			A (41 x 41 mm), C (21 x 41 mm)



Table 2/3

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Thickness (T)	A
APXE01EG	584715	1522783	114 mm	50 mm	5 mm	31 mm
APXE23EG	584710	1522784	114 mm	50 mm	5 mm	36 mm
APXE4STRUTEG	584725	1522787	144 mm	70 mm	5 mm	43 mm
APXSTRUTS6	584820		144 mm	70 mm	6 mm	43 mm

Table 3/3

Catalog Number	Article Number	E-Number	B	C
APXE01EG	584715	1522783	12 mm	19 mm
APXE23EG	584710	1522784	12 mm	19 mm
APXE4STRUTEG	584725	1522787	12 mm	19 mm
APXSTRUTS6	584820		12 mm	19 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

