

BC-M Conduit to Beam Clamp



FEATURES

Easy installation to beam flanges

Eliminates offset bending conduit


Conduit clip rotates 360 degrees

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	Flange Thickness (FT)	Torque (TQ)	Static Load	Certifications
EBC16M	172590	1500663	23.4 - 35 mm	16 mm Max	3 N·m	450N	ITB
EBC20M	172600	1500664	35 - 42 mm	16 mm Max	3 N·m	450N	ITB
EBC24M	172610		42 - 50 mm	16 mm Max	3 N·m	450N	ITB
EBC32M	172620		50 - 60 mm	16 mm Max	3 N·m	450N	ITB
EBC6M	172580		14 - 18 mm	16 mm Max	3 N·m	450N	
EBC812M	160200	1500662	18 - 30 mm	16 mm Max	3 N·m	450N	ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

