

Cable Tie with Flange Clip

FEATURES

Used to support cables from beam flanges

Requires only a hammer to install

Comes complete with zip-tie



SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	Cable Tie
2H4CTBB	170210		Spring Steel	nVent CADDY Armour	2 - 3 mm	Nylon Black
2H4CTBW	170170	1500779	Spring Steel	nVent CADDY Armour	2 - 3 mm	Nylon White
4H24CTBB	170220	1500791	Spring Steel	nVent CADDY Armour	3 - 8 mm	Nylon Black
4H24CTBRS1	170280	1500679	Stainless Steel 301 (EN 1.4310)		3 - 8 mm	Stainless Steel 302 (EN 1.4324)
4H24CTBW	170180	1500780	Spring Steel	nVent CADDY Armour	3 - 8 mm	Nylon White
4H58CTBB	170240	1500792	Spring Steel	nVent CADDY Armour	8 - 14 mm	Nylon Black
4H58CTBRS1	170300	1500686	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	Stainless Steel 302 (EN 1.4324)

Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	Cable Tie
4H58CTBW	170190	1500789	Spring Steel	nVent CADDY Armour	8 - 14 mm	Nylon White
4H912CTBB	170260	1500793	Spring Steel	nVent CADDY Armour	14 - 20 mm	Nylon Black
4H912CTBRS1	170310	1500690	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	Stainless Steel 302 (EN 1.4324)
4H912CTBW	170200	1500790	Spring Steel	nVent CADDY Armour	14 - 20 mm	Nylon White

Table 2/2

Catalog Number	Article Number	E-Number	Diameter (Ø)	Static Load	Certifications
2H4CTBB	170210		10 - 70 mm	150N	ITB
2H4CTBW	170170	1500779	10 - 70 mm	150N	ITB
4H24CTBB	170220	1500791	10 - 70 mm	150N	ITB
4H24CTBRS1	170280	1500679	25 - 51 mm	300N	
4H24CTBW	170180	1500780	10 - 70 mm	150N	ITB
4H58CTBB	170240	1500792	10 - 70 mm	150N	ITB
4H58CTBRS1	170300	1500686	25 - 51 mm	300N	
4H58CTBW	170190	1500789	10 - 70 mm	150N	ITB
4H912CTBB	170260	1500793	10 - 70 mm	150N	ITB
4H912CTBRS1	170310	1500690	25 - 51 mm	300N	
4H912CTBW	170200	1500790	10 - 70 mm	150N	ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

