

Cable Tie Holder with Flange Clip



FEATURES

Used to support cables from beam flanges

Requires only a hammer to install



SPECIFICATIONS

Table 1/2



Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	A
2H4CT	178510	1511360	Spring Steel	nVent CADDY Armour	2 - 3 mm	9 mm
4H1318CT	178545		Spring Steel	nVent CADDY Armour	21 - 28 mm	9 mm
4H24CT	178520	1511362	Spring Steel	nVent CADDY Armour	3 - 8 mm	9 mm
4H24CTR5	191021	1500709	Spring Steel	nVent CADDY Armour	3 - 8 mm	9 mm
4H24CTS1	160500		Stainless Steel 301 (EN 1.4310)		3 - 8 mm	9 mm
4H58CT	178530	1511364	Spring Steel	nVent CADDY Armour	8 - 14 mm	9 mm
4H58CTR5	191022	1500717	Spring Steel	nVent CADDY Armour	8 - 14 mm	9 mm
4H58CTS1	170430	1500637	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	9 mm

Catalog Number	Article Number	E- Number	Material	Finish	Flange Thickness (FT)	A
4H58CTSP25	172360	1511374	Spring Steel	nVent CADDY Armour	8 - 14 mm	9 mm
4H912CT	178540	1511366	Spring Steel	nVent CADDY Armour	14 - 20 mm	9 mm
4H912CTR5	191023	1500721	Spring Steel	nVent CADDY Armour	14 - 20 mm	9 mm
4H912CTS1	170700	1500645	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	9 mm
4H912CTSP25	172390	1511376	Spring Steel	nVent CADDY Armour	14 - 20 mm	9 mm

Table 2/2

Catalog Number	Article Number	E-Number	B	Static Load	Certifications
2H4CT	178510	1511360	2 mm	150N	ITB
4H1318CT	178545		2 mm	150N	
4H24CT	178520	1511362	2 mm	150N	ITB
4H24CTR5	191021	1500709	2 mm	150N	
4H24CTS1	160500		2 mm	150N	
4H58CT	178530	1511364	2 mm	150N	ITB
4H58CTR5	191022	1500717	2 mm	150N	
4H58CTS1	170430	1500637	2 mm	150N	
4H58CTSP25	172360	1511374	2 mm	150N	
4H912CT	178540	1511366	2 mm	150N	ITB
4H912CTR5	191023	1500721	2 mm	150N	
4H912CTS1	170700	1500645	2 mm	150N	
4H912CTSP25	172390	1511376	2 mm	150N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

