

Four Hole External Coupler

FEATURES

Used to create metal frames with nVent CADDY Eristrut channels



Material: Steel
Finish: Hot-Dip Galvanized


SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Strut Type	Hole Size (HS)	Thickness (T)	A
ZUA406	387810	1522653	C (21 x 41 mm)	13 mm	6 mm	184 mm
ZUA407	387820	1522651	A (41 x 41 mm)	13 mm	6 mm	184 mm

Table 2/2

Catalog Number	Article Number	E-Number	B	C
ZUA406	387810	1522653	20 mm	48 mm
ZUA407	387820	1522651	20 mm	48 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

