

J Series C Purlin Clip



FEATURES

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from purlin and bar joist

Requires only a hammer to install

Material: Spring Steel
Finish: nVent CADDY Armour


SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Flange Thickness (FT)	Hole Size (HS)	A	B
J1	170370	1511390	1.5 - 4 mm	6.8 mm	10 mm Min	36 mm
J2	171590		4.0 - 6.5 mm	6.8 mm	10 mm Min	42 mm

Table 2/2

Catalog Number	Article Number	E-Number	C	Static Load
J1	170370	1511390	44 mm	700N
J2	171590		50 mm	700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

