

Metal Strap

FEATURES

Provides variable fastening on poles, masts and pipes



Material: Stainless Steel 302 (EN 1.4324)

SPECIFICATIONS

Catalog Number	Article Number	E-Number	Strap Width	Thickness (T)
FXBF10X50MS2	591200	1500485	10 mm	0.7 mm
FXBF12X50MS2	591210	1500488	12.7 mm	0.7 mm
FXBF16X50MS2	591220		16 mm	0.7 mm
FXBF20X50MS2	591230	0682620	20 mm	0.7 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

