

OCDC Deck Hanger



FEATURES

Provide a mobile mounting hole

Attaches to decking without having to drill or punch holes

Secured between the overlap of two steel sheets


SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Hole Size (HS)	Flange Thickness (FT)
OCDC68MM	160700	1511710	Steel	nVent CADDY Armour	6.8 mm	1.0 - 2.5 mm

Table 2/2

Catalog Number	Article Number	E-Number	B	C	X	Static Load
OCDC68MM	160700	1511710	54 mm	46 mm	13 x 8.5 mm	400N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

