

Threaded Coupler for Copper-Bonded Ground Rod, Threaded



FEATURES

High-strength couplings are threaded and chamfered at both ends for easy driving

Corrosion-resistant couplings ensure permanent, low resistance copper-to-copper connections



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	E-Number	Material	Ground Rod Diameter, Nominal	Length (L)	Thread Size (TS)
CR100			Silicon Bronze	1"	99.1mm	1" UNC
CR58	158040	0632365	Bronze	5/8"	61mm	5/8" UNC
SC34	158050		Bronze	3/4"	71mm	3/4" UNC
CR34		0632364	Bronze	3/4"	76.2mm	3/4" UNC

Table 2/2

Catalog Number	Article Number	E-Number	Unit Weight	Complies With	Certifications
CR100			0.35 kg	EN IEC 62561-2	cUL, UL
CR58	158040	0632365	0.09 kg	EN IEC 62561-2	UL, cUL, CSA-US, RUS, CSA
SC34	158050		0.17 kg	IEC® EN 62561-2	

Catalog Number	Article Number	E-Number	Unit Weight	Complies With	Certifications
CR34		0632364	0.15 kg		RUS, CSA-US, UL, cUL, CSA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.