

PCB Plain Copper Busbar



FEATURES

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

Material: Copper



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-1M-12X4	550780		12 mm	4 mm	990mm	0.43 kg
PCB-2M-100X10	549750		100 mm	10 mm	2000mm	17.8 kg
PCB-2M-100X5	549640		100 mm	5 mm	2000mm	8.9 kg
PCB-2M-120X10	549760		120 mm	10 mm	2000mm	21.4 kg
PCB-2M-12X4	550790		12 mm	4 mm	1985mm	0.85 kg
PCB-2M-12X5	550770	2674025	12 mm	5 mm	1985mm	1.06 kg
PCB-2M-25X5	549600		25 mm	5 mm	2000mm	2.2 kg
PCB-2M-30X10	549700		30 mm	10 mm	2000mm	5.5 kg
PCB-2M-40X10	549710		40 mm	10 mm	2000mm	7.1 kg
PCB-2M-50X10	549720		50 mm	10 mm	2000mm	8.9 kg
PCB-2M-50X5	549610		50 mm	5 mm	2000mm	4.5 kg
PCB-2M-60X10	549730		60 mm	10 mm	2000mm	10.7 kg
PCB-2M-63X5	549620		63 mm	5 mm	2000mm	5.6 kg

Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-2M-80X10	549740		80 mm	10 mm	2000mm	14.2 kg
PCB-2M-80X5	549630		80 mm	5 mm	2000mm	7.1 kg
PCB-4M-100X10	550930		100 mm	10 mm	4000mm	35.6 kg
PCB-4M-100X5	550670		100 mm	5 mm	4000mm	17.8 kg
PCB-4M-120X10	550940		120 mm	10 mm	4000mm	42.8 kg
PCB-4M-160X10	550950		160 mm	10 mm	4000mm	57 kg
PCB-4M-20X5	550600		20 mm	5 mm	4000mm	3.56 kg

Table 2/2

Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-4M-25X5	550610		25 mm	5 mm	4000mm	4.45 kg
PCB-4M-30X10	550970		30 mm	10 mm	4000mm	10.69 kg
PCB-4M-30X5	550620		30 mm	5 mm	4000mm	5.34 kg
PCB-4M-40X10	550980		40 mm	10 mm	4000mm	14.25 kg
PCB-4M-40X5	550630		40 mm	5 mm	4000mm	7.12 kg
PCB-4M-50X10	550900		50 mm	10 mm	4000mm	17.8 kg
PCB-4M-50X5	550640		50 mm	5 mm	4000mm	8.9 kg
PCB-4M-60X10	550910		60 mm	10 mm	4000mm	21.35 kg
PCB-4M-60X5	550650		60 mm	5 mm	4000mm	10.68 kg
PCB-4M-80X10	550920		80 mm	10 mm	4000mm	28.5 kg
PCB-4M-80X5	550660		80 mm	5 mm	4000mm	14.24 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

