


Front/Rear Bottom Frames For Floor Standing Enclosures, PCU



This frame creates additional space in the bottom and can be segregated from the enclosure. It has a universal hole pattern for mounting accessories easily.

FEATURES

Description: For fixing and routing of cables or mounting of busbar. Identical hole pattern to the enclosure's frame makes all relevant accessories (e.g. CLPF, CLPK, etc) possible to mount. Fixed to the base of the enclosure by M12 screws (provided).

Side panels: PCUP supplied as an accessory.

Material: Frame in 1.75 mm steel plate, panels in 1.35 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55.

Pack quantity: 1 piece with front and back panels including mounting accessories. Add CBP for closing bottom opening.

Material: Steel
Finish: Plated
Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material
PCU3046R5	2505059	300mm	400mm	600mm	Stainless Steel

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material
PCU3048R5	2505060	300mm	400mm	800mm	Stainless Steel
PCU3066R5	2505061	300mm	599mm	600mm	Stainless Steel
PCU3068R5	2505062	300mm	599mm	800mm	Stainless Steel
PCU3086R5	2505063	300mm	800mm	600mm	Stainless Steel
PCU3088R5	2505064	300mm	800mm	800mm	Stainless Steel
PCU3106R5	2505055	300mm	999mm	600mm	Stainless Steel
PCU3108R5	2505056	300mm	999mm	800mm	Stainless Steel
PCU3126R5	2505057	300mm	1199mm	600mm	Stainless Steel
PCU3128R5	2505058	300mm	1199mm	800mm	Stainless Steel
PCU2046R5	2504978	200mm	400mm	600mm	Stainless Steel
PCU2048R5	2504979	200mm	400mm	800mm	Stainless Steel
PCU2066R5	2504980	200mm	599mm	600mm	Stainless Steel
PCU2068R5	2504981	200mm	599mm	800mm	Stainless Steel
PCU2086R5	2504982	200mm	800mm	600mm	Stainless Steel
PCU2088R5	2504983	200mm	800mm	800mm	Stainless Steel
PCU2106R5	2504974	200mm	999mm	600mm	Stainless Steel
PCU2108R5	2504975	200mm	999mm	800mm	Stainless Steel
PCU2126R5	2504976	200mm	1199mm	600mm	Stainless Steel
PCU2128R5	2504977	200mm	1199mm	800mm	Stainless Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.