

Modular Single Door, MCS



The mild steel single door combinable floor standing enclosure range, MCS, with a IP 55 protection degree, is available off the shelf in many different sizes. This enclosure range is well suited for many different applications. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E61997

NEMA/EEMAC Type 12

CSA, File No. 1442951: Type 12

IEC 62208 IP55

CE, UK CA, UL, DNV

FEATURES

Material: Frame: 1.5 mm painted steel. Door: 2 mm painted steel. Rear, roof and side panels: 1.5 mm painted steel. Mounting plate: 3 mm galvanized steel. Bottom plates: 1 mm galvanized steel.

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660. Including integrated external hole pattern.

Door: Mounted with four hinges allowing left or right hand opening. Including door frame with 25 mm hole pattern.

Rear panel: Fitted by M6 torx screws. Standard facilities for rear door mounting. RD version comes with rear door instead of rear panel.

Side panels: Supplied as an accessory.

Roof panel: Removable.

Lock: Espagnolette 4-point locking system. Does not interfere with the enclosure inner space. Standard double-bit lock with 3 mm insert. Standard inserts, cylinders, lift handles and T-handles are available as accessories.

Bottom plates: Consists of three or four (D>600) pieces.

Mounting plate: Double folded and slides into position. Adjustable in depth by steps of 25 mm, with the MPD02 accessory. Supplied, attached on the outside of the enclosure packaging.

Earthing: All panels are earthed through their fittings and are equipped with a separate earthing stud.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55 | TYPE 12 | IK 10.

Mounting requirements: Standard delivery ready for combined installation. For stand-alone installation add side panels.

Delivery: Frame with fitted door, rear panel, roof panel, bottom plates, mounting plate (not included for PER5 version) and door frame. For 400 mm wide enclosures, a mounting plate, bottom plates and door frame are not included. For enclosures 2200 mm height, delivery includes two CMB profiles mounted in depth. Delivery also includes earthing bolts. Delivered on a pallet which is identical to the width of the enclosure to allow baying without removal. All packing material is recyclable.

Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035
Body Thickness: 1.5mm
Door Thickness: 2mm

SPECIFICATIONS

Table 1/6

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS18044R5		2503055	1800mm	400mm	400mm	No
MCS18045R5		2517050	1800mm	400mm	500mm	No
MCS18046R5		2503056	1800mm	400mm	600mm	No
MCS18055PER5			1800mm	500mm	500mm	No
MCS18055R5		2503057	1800mm	500mm	500mm	Yes
MCS18064PER5		2517052	1800mm	600mm	400mm	No
MCS18064R5		2517051	1800mm	600mm	400mm	Yes
MCS18065PER5		2517054	1800mm	600mm	500mm	No
MCS18065R5		2517053	1800mm	600mm	500mm	Yes
MCS18066PER5			1800mm	600mm	600mm	No
MCS18066R5		2503058	1800mm	600mm	600mm	Yes
MCS18084PER5		2517056	1800mm	800mm	400mm	No
MCS18084R5		2517055	1800mm	800mm	400mm	Yes
MCS18085PER5		2517058	1800mm	800mm	500mm	No
MCS18085R5		2517057	1800mm	800mm	500mm	Yes
MCS18086PER5			1800mm	800mm	600mm	No
MCS18086R5		2503059	1800mm	800mm	600mm	Yes
MCS18104PER5		2517060	1800mm	1000mm	400mm	No
MCS18104R5		2517059	1800mm	1000mm	400mm	Yes
MCS18105PER5		2517062	1800mm	1000mm	500mm	No

Table 2/6

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS18105R5		2517061	1800mm	1000mm	500mm	Yes
MCS18106PER5			1800mm	1000mm	600mm	No
MCS18106R5		2503060	1800mm	1000mm	600mm	Yes

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS20044R5		2517063	2000mm	400mm	400mm	No
MCS20045R5		2517064	2000mm	400mm	500mm	No
MCS20046R5		2517065	2000mm	400mm	600mm	No
MCS20048R5		2503061	2000mm	400mm	800mm	No
MCS20055PER5			2000mm	500mm	500mm	No
MCS20055R5		2503062	2000mm	500mm	500mm	Yes
MCS20064PER5		2517067	2000mm	600mm	400mm	No
MCS20064R5		2517157	2000mm	600mm	400mm	Yes
MCS20065PER5		2517069	2000mm	600mm	500mm	No
MCS20065R5		2517068	2000mm	600mm	500mm	Yes
MCS20066PER5		2517071	2000mm	600mm	600mm	No
MCS20066R5		2517070	2000mm	600mm	600mm	Yes
MCS20068PER5		2517073	2000mm	600mm	800mm	No
MCS20068PERDR5			2000mm	600mm	800mm	No
MCS20068R5		2517072	2000mm	600mm	800mm	Yes
MCS20068RDR5			2000mm	600mm	800mm	Yes
MCS200810PERDR5	MCS200810PERDR5		2000mm	800mm	1000mm	No

Table 3/6

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS200810RDR5			2000mm	800mm	1000mm	Yes
MCS20084PER5		2517075	2000mm	800mm	400mm	No
MCS20084R5		2517074	2000mm	800mm	400mm	Yes
MCS20085PER5		2517077	2000mm	800mm	500mm	No
MCS20085R5		2517076	2000mm	800mm	500mm	Yes
MCS20086PER5		2517079	2000mm	800mm	600mm	No
MCS20086PERDR5			2000mm	800mm	600mm	No
MCS20086R5		2517078	2000mm	800mm	600mm	Yes
MCS20086RDR5			2000mm	800mm	600mm	Yes
MCS20088PER5		2517081	2000mm	800mm	800mm	No
MCS20088PERDR5			2000mm	800mm	800mm	No
MCS20088R5		2517080	2000mm	800mm	800mm	Yes
MCS20088RDR5			2000mm	800mm	800mm	Yes
MCS20104PER5		2517083	2000mm	1000mm	400mm	No
MCS20104R5		2517082	2000mm	1000mm	400mm	Yes
MCS20105PER5		2517085	2000mm	1000mm	500mm	No
MCS20105R5		2517084	2000mm	1000mm	500mm	Yes

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS20106PER5		2517087	2000mm	1000mm	600mm	No
MCS20106R5		2517086	2000mm	1000mm	600mm	Yes
MCS20108PER5			2000mm	1000mm	800mm	No

Table 4/6

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS20108PERDR5			2000mm	1000mm	800mm	No
MCS20108R5		2503063	2000mm	1000mm	800mm	Yes
MCS20108RDR5			2000mm	1000mm	800mm	Yes
MCS22066PER5	MCS22066PER5	2517089	2200mm	600mm	600mm	No
MCS22066R5	MCS22066R5	2517088	2200mm	600mm	600mm	Yes
MCS22068PER5	MCS22068PER5	2517091	2200mm	600mm	800mm	No
MCS22068R5	MCS22068R5	2517090	2200mm	600mm	800mm	Yes
MCS22086PER5	MCS22086PER5	2517093	2200mm	800mm	600mm	No
MCS22086R5	MCS22086R5	2517092	2200mm	800mm	600mm	Yes
MCS22088PER5		2517095	2200mm	800mm	800mm	No
MCS22088R5		2517094	2200mm	800mm	800mm	Yes
MCS14065PER5	MCS14065PER5	2508338	1400mm	600mm	500mm	No
MCS14065R5		2508339	1400mm	600mm	500mm	Yes
MCS14085R5		2508341	1400mm	800mm	500mm	Yes
MCS16065R5			1600mm	600mm	500mm	Yes
MCS16085R5			1600mm	800mm	500mm	Yes
MCS16065PER5	MCS16065PER5	2508342	1600mm	600mm	500mm	No
MCS16085PER5	MCS16085PER5	2508343	1600mm	800mm	500mm	No
MCS12065PER5		2508334	1200mm	600mm	500mm	No
MCS12065R5		2508335	1200mm	600mm	500mm	Yes

Table 5/6

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS12085PER5		2508336	1200mm	800mm	500mm	No
MCS12085R5		2508337	1200mm	800mm	500mm	Yes
MCS14085PER5	MCS14085PER5	2508340	1400mm	800mm	500mm	No
MCS180610PER5			1800mm	600mm	1000mm	No
MCS180610PERDR5			1800mm	600mm	1000mm	No
MCS180610R5			1800mm	600mm	1000mm	Yes
MCS180610RDR5			1800mm	600mm	1000mm	Yes
MCS180810PER5			1800mm	800mm	1000mm	No


Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS180810PERDR5			1800mm	800mm	1000mm	No
MCS180810R5			1800mm	800mm	1000mm	Yes
MCS180810RDR5			1800mm	800mm	1000mm	Yes
MCS200610PER5			2000mm	600mm	1000mm	No
MCS200610PERDR5			2000mm	600mm	1000mm	No
MCS200610R5			2000mm	600mm	1000mm	Yes
MCS200610RDR5			2000mm	600mm	1000mm	Yes
MCS200810PER5	MCS200810PER5		2000mm	800mm	1000mm	No
MCS200810R5	MCS200810R5		2000mm	800mm	1000mm	Yes
MCS220610PER5			2200mm	600mm	1000mm	No
MCS220610PERDR5			2200mm	600mm	1000mm	No
MCS220610R5			2200mm	600mm	1000mm	Yes

Table 6/6

Catalog Number	Article Number	E-Number	Height (H)	Width (W)	Depth (D)	Mounting Plate Included
MCS220610RDR5			2200mm	600mm	1000mm	Yes
MCS220810PER5	MCS220810PER5		2200mm	800mm	1000mm	No
MCS220810PERDR5			2200mm	800mm	1000mm	No
MCS220810R5	MCS220810R5		2200mm	800mm	1000mm	Yes
MCS220810RDR5			2200mm	800mm	1000mm	Yes

ADDITIONAL PRODUCT DETAILS

SPM mild steel side panels must be ordered separately to close the cabinets (individual or assembled), in order to maintain the protection rating.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

