

Mounting Plate, MP

The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

FEATURES

Description: Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.

Material: 3 mm galvanized steel.

Pack quantity: 1 piece.

Maximum load: 6000 N.

Mounting requirements: Use MPA for mounting the MP inside the enclosure. Adjustable in depth with MPD accessory.



Material: Mild Steel
Finish: Galvanized
Thickness: 3mm

SPECIFICATIONS

Table 1/2

Catalog Number	E-Number	Height	Width	Depth	Mounting Plate Height	Mounting Plate Height
MP1606	2517240	1600mm	600mm	25mm	58.81mm	1494mm
MP1608	2517241	1600mm	800mm	25mm	58.82mm	1494mm
MP1806	2517244	1800mm	600mm	25mm	66.7mm	1694mm
MP1808	2517245	1800mm	800mm	25mm	66.7mm	1694mm
MP2006	2517248	2000mm	600mm	25mm	74.56mm	1894mm
MP2008	2517249	2000mm	800mm	25mm	74.56mm	1894mm
MP1212	2503131	1200mm	1200mm	25mm	43.07mm	1094mm
MP1612	2517243	1600mm	1200mm	25mm	58.82mm	1494mm
MP1812	2517247	1800mm	1200mm	25mm	66.7mm	1694mm
MP1816	2503136	1800mm	1600mm	25mm	66.7mm	1694mm
MP2012	2517251	2000mm	1200mm	25mm	74.56mm	1894mm

Catalog Number	E-Number	Height	Width	Depth	Mounting Plate Height	Mounting Plate Height
MP2016	2503139	2000mm	1600mm	25mm	74.56mm	1894mm
MP1206	2517290	1200mm	600mm	25mm	43.07mm	1094mm
MP1208	2517291	1200mm	800mm	25mm	43.07mm	1094mm
MP1406	2517292	1400mm	600mm	25mm	50.94mm	1294mm
MP1408	2517293	1400mm	800mm	25mm	50.94mm	1294mm
MP1610	2517242	1600mm	1000mm	25mm	58.82mm	1494mm
MP1810	2517246	1800mm	1000mm	25mm	66.7mm	1694mm
MP2010	2517250	2000mm	1000mm	25mm	74.56mm	1894mm
MP2210	2517254	2200mm	1000mm	25mm	82.44mm	2094mm

Table 2/2

Catalog Number	E-Number	Height	Width	Depth	Mounting Plate Height	Mounting Plate Height
MP2212	2517255	2200mm	1200mm	25mm	82.44mm	2094mm
MP1804	2503134	1800mm	400mm	25mm	66.7mm	1694mm
MP1805	2503135	1800mm	500mm	25mm	66.7mm	1694mm
MP2004	2503137	2000mm	400mm	25mm	74.56mm	1894mm
MP2005	2503138	2000mm	500mm	25mm	74.56mm	1894mm
MP2206	2517252	2200mm	600mm	25mm	82.44mm	2094mm
MP2208	2517253	2200mm	800mm	25mm	82.44mm	2094mm
MP1410	2503132	1400mm	1000mm	25mm	50.94mm	1294mm
MP1412	2503133	1400mm	1200mm	25mm	50.94mm	1294mm

ADDITIONAL PRODUCT DETAILS

Note: for 1600 mm width, the mounting plate is delivered as two 800 mm width mounting plates and one filler plate.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

