

Plain Doors, DN



This door replaces the rear panel in a floor standing enclosure to allow for rear access of equipment installed in the front, or for using back to back mounting plates to increase the enclosure's mounting space.

FEATURES

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNMK (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNMK if no door was fitted previously.

Pack quantity: 1 piece.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035

SPECIFICATIONS

Table 1/3

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN1106R5	2505098	1082mm	593mm	17mm	Plain	Free-Standing

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN1206LR5		1182mm	593mm	17mm	Left Door	Free-Standing
DN1206R5		1182mm	593mm	17mm	Plain	Free-Standing
DN1206RR5		1182mm	593mm	17mm	Right Door	Free-Standing
DN1208R5	2505099	1182mm	793mm	17mm	Plain	Free-Standing
DN1405LR5		1382mm	493mm	17mm	Left Door	Free-Standing
DN1405RR5		1382mm	493mm	17mm	Right Door	Free-Standing
DN1406LR5		1382mm	593mm	17mm	Left Door	Free-Standing
DN1406R5		1382mm	593mm	17mm	Plain	Free-Standing
DN1406RR5		1382mm	793mm	17mm	Right Door	Free-Standing
DN1408R5		1382mm	793mm	17mm	Plain	Free-Standing
DN1606LR5		1582mm	593mm	17mm	Left Door	Free-Standing
DN1606R5		1582mm	593mm	17mm	Plain	Free-Standing
DN1606RR5		1582mm	593mm	17mm	Right Door	Free-Standing
DN1608R5		1582mm	793mm	17mm	Plain	Free-Standing
DN1610R5		1582mm	993mm	17mm	Plain	Free-Standing
DN1804LR5		1782mm	393mm	17mm	Left Door	Free-Standing
DN1804RR5		1782mm	393mm	17mm	Right Door	Free-Standing
DN1805LR5		1782mm	493mm	17mm	Left Door	Free-Standing
DN1805R5		1782mm	493mm	17mm	Plain	Free-Standing

Table 2/3

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN1805RR5		1782mm	493mm	17mm	Right Door	Free-Standing
DN1806LR5		1782mm	593mm	17mm	Left Door	Free-Standing
DN1806R5		1782mm	593mm	17mm	Plain	Free-Standing
DN1806RR5		1782mm	593mm	17mm	Right Door	Free-Standing
DN1808LR5		1782mm	793mm	17mm	Left Door	Free-Standing
DN1808R5		1782mm	793mm	17mm	Plain	Free-Standing
DN1808RR5		1782mm	793mm	17mm	Right Door	Free-Standing
DN1810R5		1782mm	993mm	17mm	Plain	Free-Standing
DN2004LR5		1982mm	393mm	17mm	Left Door	Free-Standing
DN2004RR5		1982mm	393mm	17mm	Right Door	Free-Standing
DN2005LR5		1982mm	493mm	17mm	Left Door	Free-Standing
DN2005R5		1982mm	493mm	17mm	Plain	Free-Standing
DN2005RR5		1982mm	493mm	17mm	Right Door	Free-Standing
DN2006LR5		1982mm	593mm	17mm	Left Door	Free-Standing
DN2006R5		1982mm	593mm	17mm	Plain	Free-Standing

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN2006RR5		1982mm	593mm	17mm	Right Door	Free-Standing
DN2008LR5		1982mm	793mm	17mm	Left Door	Free-Standing
DN2008R5		1982mm	793mm	17mm	Plain	Free-Standing
DN2008RR5		1982mm	793mm	17mm	Right Door	Free-Standing
DN2010R5		1982mm	993mm	17mm	Plain	Free-Standing

Table 3/3

Catalog Number	E-Number	Height	Width	Depth	Door Type	Product Family
DN2205LR5		2182mm	493mm	17mm	Left Door	Free-Standing
DN2205RR5		2182mm	493mm	17mm	Right Door	Free-Standing
DN2206LR5		2182mm	593mm	17mm	Left Door	Free-Standing
DN2206R5		2182mm	593mm	17mm	Plain	Free-Standing
DN2206RR5		2182mm	593mm	17mm	Right Door	Free-Standing
DN2208R5	2505102	2182mm	793mm	17mm	Plain	Free-Standing
DN1804R5		1782mm	393mm	17mm	Plain	Free-Standing
DN2004R5		1982mm	393mm	17mm	Plain	Free-Standing
DN2204R5	2505101	2182mm	393mm	17mm	Plain	Free-Standing
DN2210R5	2505100	2182mm	993mm	17mm	Plain	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

