

Side Panels For Floor Standing Enclosures, PCUP



The extra space created by an extension frame is closed off by using these panels in order to maintain the protection degree and restrict access to the extra space.

FEATURES

Description: For covering the sides of the bottom cabling frame PCU. Mounted with 4 screws and new patented retainers.

Material: 1.35 mm steel plate.

Finish: RAL 7035 structured powder coating.

Pack quantity: 2 panels with mounting accessories.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035
Thickness: 1.35mm

SPECIFICATIONS

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material
PCUP306R5	2504678	300mm	599mm	12mm	Mild Steel
PCUP308R5	2504679	300mm	800mm	12mm	Mild Steel
PCUP206R5	2504676	200mm	599mm	12mm	Mild Steel
PCUP208R5	2504677	200mm	800mm	12mm	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.